





Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Modular Cut-out
Installed device	ComPact: fixed INS100 - control: direct front rotary handle - vertical installation ComPact: fixed INS125 - control: direct front rotary handle - vertical installation ComPact: fixed INS160 - control: direct front rotary handle - vertical installation Acti 9: fixed C120 without earth leakage protection - control: toggle TeSys: fixed GV3 Acti 9: fixed iC120 without earth leakage protection - control: toggle Multi9: fixed NG125 without earth leakage protection - control: toggle Multi9: fixed NG125 NA - control: toggle ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle TeSys: fixed TeSys U - horizontal installation Acti 9: fixed C120 with earth leakage protection - control: toggle Acti 9: fixed iC120 with earth leakage protection - control: toggle Multi9: fixed NG125 with earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation

Poles description	1 x 3P: modular rail support: INS100 vertical installation 1 x 4P: modular rail support: INS100 vertical installation 1 x 3P: modular rail support: INS125 vertical installation 1 x 4P: modular rail support: INS125 vertical installation 1 x 3P: modular rail support: INS160 vertical installation 1 x 4P: modular rail support: INS160 vertical installation 1 x 3P: modular rail support: C120 1 x 4P: modular rail support: C120 7 x 3P: modular rail support: GV3 1 x 3P: modular rail support: iC120 1 x 4P: modular rail support: iC120 1 x 3P: modular rail support: NG125 1 x 4P: modular rail support: NG125 1 x 3P: modular rail support: NG125 NA 1 x 4P: modular rail support: NG125 NA 1 x 3P: modular rail support: NG160 1 x 4P: modular rail support: NG160 1 x 3P: modular rail support: NG160 NA 1 x 4P: modular rail support: NG160 NA 9 x 3P: modular rail support: TeSys U horizontal installation 1 x 3P or 4P: modular rail support: NSXm vertical installation 5 x 3P: mounting plate support: NSXm vertical installation 4 x 4P: mounting plate support: NSXm vertical installation 4 x 3P or 4P: mounting plate support: NSXm vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Connection position	Direct connection
9 mm pitches	48
Number of 18 mm modules per row	24
Number of vertical modules [50 mm]	5
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	250 mm
Width	500 mm
Net weight	0.92 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	920.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	27.2 cm
Package 2 Length	52.0 cm
Package 2 Weight	9.455 kg
Unit Type of Package 3	P12
Number of Units in Package 3	270
Package 3 Height	94.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	267.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product