



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Modular
Installed device	Acti 9: fixed modular device Multi9: fixed modular device ComPact: fixed INS100 - control: direct front rotary handle - vertical installation ComPact: fixed INS125 - control: direct front rotary handle - vertical installation ComPact: fixed INS160 - control: direct front rotary handle - vertical installation ComPact: fixed INS40 - control: direct front rotary handle - vertical installation ComPact: fixed INS63 - control: direct front rotary handle - vertical installation
Poles description	4 x 3P: modular rail support: INS100 vertical installation 4 x 4P: modular rail support: INS100 vertical installation 4 x 3P: modular rail support: INS125 vertical installation 4 x 4P: modular rail support: INS125 vertical installation 4 x 3P: modular rail support: INS160 vertical installation 4 x 4P: modular rail support: INS160 vertical installation 4 x 3P: modular rail support: INS40 vertical installation 4 x 4P: modular rail support: INS40 vertical installation 4 x 3P: modular rail support: INS63 vertical installation 4 x 4P: modular rail support: INS63 vertical installation

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Connection position	Direct connection
9 mm pitches	72
Number of 18 mm modules per row	36
Number of vertical modules [50 mm]	4
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	200 mm
Width	850 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	1.22 kg
Quantity per set	Set of 1
Functional unit	<p>850 mm PrismaSeT G floor-standing enclosure ComPact INS100 fixed direct front rotary handle vertical 3P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS100 fixed direct front rotary handle vertical 4P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS125 fixed direct front rotary handle vertical 3P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS125 fixed direct front rotary handle vertical 4P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS160 fixed direct front rotary handle vertical 3P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS160 fixed direct front rotary handle vertical 4P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS40 fixed direct front rotary handle vertical 3P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS40 fixed direct front rotary handle vertical 4P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 3P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure ComPact INS63 fixed direct front rotary handle vertical 4P 4 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure Acti 9 modular device fixed 72 direct 4</p> <p>850 mm PrismaSeT G floor-standing enclosure Multi9 modular device fixed 72 direct 4</p>

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	20 cm
Package 1 Length	75 cm
Package 1 Weight	1.222 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	10.5 cm
Package 2 Width	22 cm
Package 2 Length	76 cm
Package 2 Weight	7.743 kg
Unit Type of Package 3	P12
Number of Units in Package 3	192
Package 3 Height	85 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	259.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
