

# LVS03225

Front plate, PrismaSeT P, for Vigi NSXm up to 160, 5M, Vertical, Fixed, Toggle/ rotary handle, W400 5M, white, RAL 9003



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm without earth leakage protection - control: direct rotary handle - vertical installation
Poles description	1 x 3P or 4P: mounting plate support: NSXm vertical installation
Operating position	Vertical

## Complementary

Enclosure/cubicle description	Cubicle duct - width 400 mm depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	5
Standards	IEC 61496-1 IEC 61439-2
Product certifications	ASTA
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	250 mm
Quantity per set	Set of 1
Functional unit	400 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed toggle vertical 3P or 4P 1 direct 8 400 mm 400 mm PrismaSeT P cubicle ComPact NSXm without fixed direct rotary handle vertical 3P or 4P 1 direct 8 400 mm 400 mm PrismaSeT P cubicle ComPact NSXm with fixed toggle vertical 3P or 4P 1 direct 8

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	26 cm
Package 1 Length	26.5 cm
Package 1 Weight	554 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17 cm

Package 2 Width	27.5 cm
Package 2 Length	27.5 cm
Package 2 Weight	5.687 kg
Unit Type of Package 3	BB1
Number of Units in Package 3	10
Package 3 Height	17 cm
Package 3 Width	27.5 cm
Package 3 Length	27.5 cm
Package 3 Weight	5.687 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product