

LVS03231

Front plate, PrismaSeT G, for INS-INV100/160/250, 4M, horizontal, fixed, front handle, W600/ W600+W300, white, RAL 9003



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Installed device	ComPact: fixed INS250 - control: direct front rotary handle - horizontal installation ComPact: fixed INV100 - control: direct front rotary handle - horizontal installation ComPact: fixed INV160 - control: direct front rotary handle - horizontal installation ComPact: fixed INV200 - control: direct front rotary handle - horizontal installation ComPact: fixed INV250 - control: direct front rotary handle - horizontal installation
Poles description	1 x 3P: mounting plate support: INS250 horizontal installation 1 x 4P: mounting plate support: INS250 horizontal installation 1 x 3P: mounting plate support: INV100 horizontal installation 1 x 4P: mounting plate support: INV100 horizontal installation 1 x 3P: mounting plate support: INV250 horizontal installation 1 x 4P: mounting plate support: INV250 horizontal installation 1 x 3P: mounting plate support: INV160 horizontal installation 1 x 4P: mounting plate support: INV160 horizontal installation 1 x 3P: mounting plate support: INV200 horizontal installation 1 x 4P: mounting plate support: INV200 horizontal installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection position	Direct connection Connection block
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Colour	White (RAL 9003)
Height	200 mm
Width	500 mm
Net weight	0.8 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	21.5 cm
Package 1 Length	51.4 cm
Package 1 Weight	789.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	22.0 cm
Package 2 Length	53.2 cm
Package 2 Weight	8.097 kg
Unit Type of Package 3	P12
Number of Units in Package 3	270
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	229.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations