

LVS03247

Front plate, PrismaSeT P and G, for INS-INV250 changeover, 5M, vertical, fixed, W600, white, RAL 9003

Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed INS250 source changeover - control: direct front rotary handle - vertical installation
Poles description	1 x 3P: mounting plate support: INS250 source changeover vertical installation 1 x 4P: mounting plate support: INS250 source changeover vertical installation 2 x 3P: mounting plate support: INS250 source changeover vertical installation 2 x 4P: mounting plate support: INS250 source changeover vertical installation
Operating position	Vertical

Complementary







Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection position	Front connection Direct connection
Number of vertical modules [50 mm]	5
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	250 mm
Width	500 mm
Net weight	0.9 kg
Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 3P 1 direct 9 650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 4P 1 direct 9 600 mm PrismaSeT G floor-standing enclosure ComPact INS250 source changeover fixed direct front rotary handle vertical 3P 2 front connection 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INS250 source changeover fixed direct front rotary handle vertical 3P 2 front connection 10 600 mm PrismaSeT G floor-standing enclosure ComPact INS250 source changeover fixed direct front rotary handle vertical 4P 2 front connection 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INS250 source changeover fixed direct front rotary handle vertical 4P 2 front connection 10

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	904.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	27.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	9.249 kg
Unit Type of Package 3	P12
Number of Units in Package 3	90
Package 3 Height	41.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	94.5 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
BVB	 Accepted
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No