

# LVS03259

Front Plate, PrismaSeT G, Cut-out type, for NSX250 3P/4P vertical fixed toggle, 9M, enclosure W600mm



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct
Type of front plate	Cut-out
Installed device	ComPact: fixed INV100 - control: direct front rotary handle - vertical installation ComPact: fixed INV160 - control: direct front rotary handle - vertical installation ComPact: fixed INV200 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 4P: mounting plate support: INV100 vertical installation 1 x 4P: mounting plate support: INV160 vertical installation 1 x 4P: mounting plate support: INV200 vertical installation 1 x 4P: mounting plate support: INV250 vertical installation 1 x 4P: mounting plate support: NSX100...160 vertical installation 1 x 4P: mounting plate support: NSX250 vertical installation
Operating position	Superposed

## Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Number of vertical modules [50 mm]	12
Standards	IEC 61439-2 NF C 15-100 IEC 61439-1
Product certifications	ASTA
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	600 mm
Width	300 mm
Net weight	1.2 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	Set of 1
Functional unit	300 mm PrismaSeT G floor-standing duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G wall-mounted duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G floor-standing duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G wall-mounted duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G floor-standing duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G wall-mounted duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 12 300 mm PrismaSeT G floor-standing duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact NSX100...160 without fixed toggle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact NSX100...160 without fixed toggle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact NSX250 without fixed toggle vertical 4P 1 direct 300 mm PrismaSeT G wall-mounted duct ComPact NSX250 without fixed toggle vertical 4P 1 direct 300 mm PrismaSeT G floor-standing duct ComPact NSX250 with fixed toggle vertical 4P 1 direct 16 300 mm PrismaSeT G wall-mounted duct ComPact NSX250 with fixed toggle vertical 4P 1 direct 16

## Environment

IP degree of protection	IP30
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	25 cm
Package 1 Length	60 cm
Package 1 Weight	1.1 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	16.5 cm
Package 2 Width	53.5 cm
Package 2 Length	82 cm
Package 2 Weight	7.571 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	72.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product