



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Type of front plate	Cut-out
Installed device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed EZC400 - control: toggle - horizontal installation EasyPact: fixed EZC630 - control: toggle - horizontal installation
Poles description	1 x 3P: mounting plate support: CVS400 horizontal installation 1 x 4P: mounting plate support: CVS400 horizontal installation 1 x 3P: mounting plate support: CVS630 horizontal installation 1 x 4P: mounting plate support: CVS630 horizontal installation 1 x 3P: mounting plate support: EZC400 horizontal installation 1 x 4P: mounting plate support: EZC400 horizontal installation 1 x 3P: mounting plate support: EZC630 horizontal installation 1 x 4P: mounting plate support: EZC630 horizontal installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	6
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	300 mm
Width	500 mm
Net weight	1.18 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	Set of 1
Functional unit	<p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS400 without fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact CVS630 without fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC400 fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 9</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 3P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G floor-standing enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 6</p> <p>600 + 300 mm PrismaSeT G wall-mounted enclosure + duct EasyPact EZC630 fixed toggle horizontal 4P 1 direct with long terminal shield 6</p>

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	31.5 cm
Package 1 Length	51.5 cm

Package 1 Weight	1.181 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	33.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	12.152 kg
Unit Type of Package 3	P12
Number of Units in Package 3	180
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	230.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product