

LVS03273

Front Plate, PrismaSeT P & G, Cut-out type,
for CVS 630 3P/4P vertical fixed toggle, 9M,
enclosure W600mm



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Type of front plate	Cut-out
Installed device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed EZC400 - control: toggle - vertical installation EasyPact: fixed EZC630 - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: CVS400 vertical installation 1 x 4P: mounting plate support: CVS400 vertical installation 1 x 3P: mounting plate support: CVS630 vertical installation 1 x 4P: mounting plate support: CVS630 vertical installation 1 x 3P: mounting plate support: EZC400 vertical installation 1 x 4P: mounting plate support: EZC400 vertical installation 1 x 3P: mounting plate support: EZC630 vertical installation 1 x 4P: mounting plate support: EZC630 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	450 mm
Width	500 mm

Net weight	1.76 kg
Quantity per set	Set of 1
Functional unit	<p>650 mm 400 mm PrismaSeT P cubicle EasyPact CVS400 without fixed toggle vertical 3P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact CVS400 without fixed toggle vertical 4P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact CVS630 without fixed toggle vertical 3P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact CVS630 without fixed toggle vertical 4P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact EZC400 fixed toggle vertical 3P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact EZC400 fixed toggle vertical 4P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact EZC630 fixed toggle vertical 3P 1 direct 13</p> <p>650 mm 400 mm PrismaSeT P cubicle EasyPact EZC630 fixed toggle vertical 4P 1 direct 13</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact CVS400 without fixed toggle vertical 3P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact CVS400 without fixed toggle vertical 3P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact CVS400 without fixed toggle vertical 4P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact CVS400 without fixed toggle vertical 4P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact CVS630 without fixed toggle vertical 3P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact CVS630 without fixed toggle vertical 3P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact CVS630 without fixed toggle vertical 4P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact CVS630 without fixed toggle vertical 4P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact EZC400 fixed toggle vertical 3P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact EZC400 fixed toggle vertical 3P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact EZC400 fixed toggle vertical 4P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact EZC400 fixed toggle vertical 4P 1 direct with long terminal shield 12</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact EZC630 fixed toggle vertical 3P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact EZC630 fixed toggle vertical 3P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G floor-standing enclosure EasyPact EZC630 fixed toggle vertical 4P 1 direct with long terminal shield 13</p> <p>600 mm PrismaSeT G wall-mounted enclosure EasyPact EZC630 fixed toggle vertical 4P 1 direct with long terminal shield 13</p>

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	46.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.778 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	11.000 cm
Package 2 Width	52.000 cm
Package 2 Length	52.000 cm
Package 2 Weight	11.206 kg
Unit Type of Package 3	P12
Number of Units in Package 3	96
Package 3 Height	97.000 cm

Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	190.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product