

# LVS03301

Front plate, PrismaSeT G, for NSX/CVS 250, 4M, horizontal, fixed, rotary handle, cut-out, W850



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Installed device	EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100...160 integrated earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 integrated earth leakage protection - control: direct front rotary handle - horizontal installation Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI Enerlin'X: fixed FDM121 - control: remote control - vertical installation
Poles description	1 x 3P: mounting plate support: CVS100...160 horizontal installation 1 x 4P: mounting plate support: CVS100...160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation 1 x 3P: mounting plate support: NSX100...160 horizontal installation 1 x 4P: mounting plate support: NSX100...160 horizontal installation 1 x 3P: mounting plate support: NSX250 horizontal installation 1 x 4P: mounting plate support: NSX250 horizontal installation
Operating position	Horizontal

## Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Surface finish	Textured Matt

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	200 mm
Width	750 mm
Quantity per set	Set of 1
Functional unit	850 mm PrismaSeT G floor-standing enclosure human-switchboard interface 96 x 96 mm device 1 4 850 mm PrismaSeT G floor-standing enclosure human-switchboard interface HSI 1 4 850 mm PrismaSeT G floor-standing enclosure Enerlin'X FDM121 fixed remote control vertical 1 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100...160 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100...160 integrated fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 integrated fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4

## Environment

IP degree of protection	IP30
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	20.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	1.445 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	10.5 cm
Package 2 Width	22.0 cm
Package 2 Length	76.0 cm
Package 2 Weight	8.937 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	35.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	101.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product