



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct PrismaSeT PrismaSeT Pack 250 duct
Type of front plate	Cut-out
Installed device	FuPact: fixed ISFT250 - control: fuse carriers handle - vertical installation
Poles description	1 x 3P: mounting plate support: ISFT250 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	450 mm
Width	250 mm
Net weight	0.74 kg
Quantity per set	Set of 1
Functional unit	300 mm PrismaSeT G floor-standing duct FuPact ISFT250 fixed fuse carriers handle vertical 3P 1 direct 9 300 mm PrismaSeT G wall-mounted duct FuPact ISFT250 fixed fuse carriers handle vertical 3P 1 direct 9 300 mm Prisma Pack 250 Pack enclosure FuPact ISFT250 fixed fuse carriers handle vertical 3P 1 direct 9

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.5 cm
Package 1 Length	46.0 cm
Package 1 Weight	747.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	17.0 cm
Package 2 Width	27.5 cm
Package 2 Length	52.5 cm
Package 2 Weight	7.679 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	31.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	57.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product