

## Main

|                                    |                                                                                                                                                          |
|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                              | PrismaSeT                                                                                                                                                |
| Range of product                   | PrismaSeT G<br>PrismaSeT P                                                                                                                               |
| Product or component type          | Front plate                                                                                                                                              |
| Accessory / separate part category | Installation accessory                                                                                                                                   |
| Range compatibility                | PrismaSeT PrismaSeT G enclosure<br>PrismaSeT PrismaSeT P cubicle                                                                                         |
| Type of front plate                | Transparent                                                                                                                                              |
| Installed device                   | Power meters: kilowatt-hour meters - vertical installation                                                                                               |
| Poles description                  | 2 x 4P: mounting plate support: kilowatt-hour meters vertical installation<br>2 x 3P: mounting plate support: kilowatt-hour meters vertical installation |

## Complementary

|                                    |                                                                                                                                                                                                                                                                                     |
|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Enclosure/cubicle description      | Floor-standing enclosure - width 600 mm<br>Wall-mounted enclosure - width 600 mm<br>Cubicle - width 650 mm depth 400 mm<br>Pack enclosure - width 555 mm                                                                                                                            |
| Number of vertical modules [50 mm] | 9                                                                                                                                                                                                                                                                                   |
| Standards                          | IEC 61439-2<br>IEC 61439-1                                                                                                                                                                                                                                                          |
| Product certifications             | ASTA                                                                                                                                                                                                                                                                                |
| Material                           | Glass                                                                                                                                                                                                                                                                               |
| Surface finish                     | Matt<br>Textured                                                                                                                                                                                                                                                                    |
| Protective treatment               | Electrophoresis treatment and hot-polymerised polyester epoxy powder                                                                                                                                                                                                                |
| Colour                             | White (RAL 9003)                                                                                                                                                                                                                                                                    |
| Height                             | 450 mm                                                                                                                                                                                                                                                                              |
| Width                              | 500 mm                                                                                                                                                                                                                                                                              |
| Net weight                         | 2.04 kg                                                                                                                                                                                                                                                                             |
| Quantity per set                   | Set of 1                                                                                                                                                                                                                                                                            |
| Functional unit                    | 600 mm PrismaSeT G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 9<br>600 mm PrismaSeT G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 9<br>650 mm 400 mm PrismaSeT P cubicle power meters kilowatt-hour meters vertical 4P 2 9 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 2.000 cm  |
| Package 1 Width              | 46.000 cm |
| Package 1 Length             | 50.000 cm |
| Package 1 Weight             | 2.114 kg  |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 6         |

|                              |            |
|------------------------------|------------|
| Package 2 Height             | 16.500 cm  |
| Package 2 Width              | 53.500 cm  |
| Package 2 Length             | 83.000 cm  |
| Package 2 Weight             | 13.670 kg  |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 12         |
| Package 3 Height             | 30.000 cm  |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 34.000 kg  |

## Offer Sustainability

|                             |                                                                                                                                                                    |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| BVB                         |  Accepted                                                                         |
| REACH Regulation            |  REACH Declaration                                                                |
| REACH free of SVHC          | Yes                                                                                                                                                                |
| EU RoHS Directive           | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free      | Yes                                                                                                                                                                |
| Mercury free                | Yes                                                                                                                                                                |
| RoHS exemption information  |  Yes                                                                              |
| China RoHS Regulation       |  China RoHS Declaration                                                           |
| Environmental Disclosure    |  Product Environmental Profile                                                    |
| Circularity Profile         | No need of specific recycling operations                                                                                                                           |
| PVC free                    | Yes                                                                                                                                                                |
| Halogen content performance | Halogen free plastic parts product                                                                                                                                 |
| Take-back                   | No                                                                                                                                                                 |