



## Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct PrismaSeT PrismaSeT P duct
Type of front plate	Transparent
Installed device	Power meters: kilowatt-hour meters - vertical installation
Poles description	1 x 4P: mounting plate support: kilowatt-hour meters vertical installation

## Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Glass
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	450 mm
Width	300 mm
Net weight	1.14 kg
Quantity per set	Set of 1
Functional unit	400 mm 400 mm PrismaSeT P cubicle 300 mm PrismaSeT G floor-standing duct power meters kilowatt-hour meters vertical 4P 1 9 300 mm PrismaSeT G wall-mounted duct power meters kilowatt-hour meters vertical 4P 1 9

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	26.5 cm
Package 1 Length	46.5 cm
Package 1 Weight	1.368 kg
Unit Type of Package 2	S04
Number of Units in Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Package 2 Length	60.0 cm
Package 2 Weight	10.966 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product