

LVS03416

Mounting plate, PrismaSeT P, for NSXm
+FC 160A 3P/4P, vertical toggle/direct rotary
handle, 5M, W650mm



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle Linergy Linergy FC device feeder ComPact ComPact NSXm circuit breaker
Installation description	Cubicle - width 650 mm depth 400 mm
Installed device	ComPact: NSXm without earth leakage protection - control: toggle ComPact: NSXm without earth leakage protection - control: direct rotary handle ComPact: NSXm integrated earth leakage protection - control: toggle ComPact: NSXm integrated earth leakage protection - control: direct rotary handle
Poles description	5 x 3P: fixed NSXm vertical installation 4 x 4P: fixed NSXm vertical installation
Number of vertical modules [50 mm]	5 module(s): NSXm without earth leakage protection , Linergy FC 5 module(s): NSXm integrated earth leakage protection , Linergy FC
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	580 mm
Height	154 mm
Depth	23 mm
Net weight	2.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	15 cm
Package 1 Length	58 cm
Package 1 Weight	2.134 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm

Package 2 Length	60 cm
Package 2 Weight	9.288 kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	72 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	87 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product