





Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm

Installed device	<p>ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NSX100...160 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: drawout NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NSX250 without earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: drawout NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NSX250 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NSX100...160 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: drawout NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: plug-in NSX250 with earth leakage protection - control: motor mechanism - vertical installation</p> <p>ComPact: drawout NSX250 with earth leakage protection - control: toggle - vertical installation</p> <p>ComPact: drawout NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>ComPact: drawout NSX250 with earth leakage protection - control: motor mechanism - vertical installation</p>
Poles description	<p>4 x 3P: plug-in NSX100...160 vertical installation</p> <p>3 x 4P: plug-in NSX100...160 vertical installation</p> <p>2 x 3P: drawout NSX100...160 vertical installation</p> <p>2 x 4P: drawout NSX100...160 vertical installation</p> <p>4 x 3P: plug-in NSX250 vertical installation</p> <p>3 x 4P: plug-in NSX250 vertical installation</p> <p>2 x 3P: drawout NSX250 vertical installation</p> <p>2 x 4P: drawout NSX250 vertical installation</p>

Number of vertical modules [50 mm]	8 module(s): NSX100...160 without earth leakage protection , direct in 650 mm Widecubicle 9 module(s): NSX250 without earth leakage protection , direct in 650 mm Widecubicle 10 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 11 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle 7 module(s): NSX100...160 without earth leakage protection , Linergy FC in 650 mm Widecubicle 9 module(s): NSX100...160 without earth leakage protection , direct in 650 mm Widecubicle 8 module(s): NSX250 without earth leakage protection , Linergy FC in 650 mm Widecubicle 10 module(s): NSX250 without earth leakage protection , direct in 650 mm Widecubicle 9 module(s): NSX100...160 with earth leakage protection , Linergy FC in 650 mm Widecubicle 11 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 9 module(s): NSX100...160 with earth leakage protection , direct in 650 mm Widecubicle 10 module(s): NSX250 with earth leakage protection , Linergy FC in 650 mm Widecubicle 12 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle 10 module(s): NSX250 with earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured Matt
Colour	White (RAL 9003)
Width	603 mm
Height	202 mm
Depth	372 mm

Net weight

3.2 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	20.500 cm
Package 1 Length	58.000 cm
Package 1 Weight	3.207 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	20.223 kg
Unit Type of Package 3	P12
Number of Units in Package 3	72
Package 3 Height	102.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	255.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product