

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Type of front plate	Cut-out
Installed device	ComPact: fixed INV800...1250 + NS800...1250 without earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: INV800...1250 + NS800...1250 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Cubicle - width 650 + 150 mm depth 400 mm
Connection position	Front connection
Number of vertical modules [50 mm]	12
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	600 mm
Width	500 mm
Net weight	2.8 kg
Functional unit	650 + 150 mm 400 mm PrismaSeT P cubicle ComPact INV800...1250 + NS800...1250 without fixed toggle vertical 3P 1 front connection

Environment







IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	50.500 cm
Package 1 Length	60.000 cm
Package 1 Weight	2.896 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	26.500 cm
Package 2 Width	60.000 cm

Package 2 Length	79.000 cm
Package 2 Weight	13.440 kg
Unit Type of Package 3	P06
Number of Units in Package 3	12
Package 3 Height	95.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	46.000 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
BVB	 Accepted
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No