

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	Masterpact: fixed NT06...10 - control: toggle - vertical installation Masterpact: fixed NT12 - control: toggle - vertical installation Masterpact: fixed NT16 - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: NT06...10 vertical installation 1 x 3P: mounting plate support: NT12 vertical installation 1 x 3P: mounting plate support: NT16 vertical installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Cubicle duct - width 400 mm depth 400 mm
Connection position	Front connection
Number of vertical modules [50 mm]	11
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	550 mm
Width	321 mm
Net weight	1.88 kg
Quantity per set	Set of 1
Functional unit	400 mm 400 mm PrismaSeT P cubicle Masterpact NT06...10 fixed toggle vertical 3P 1 front connection 36 400 mm 400 mm PrismaSeT P cubicle Masterpact NT12 fixed toggle vertical 3P 1 front connection 36 400 mm 400 mm PrismaSeT P cubicle Masterpact NT16 fixed toggle vertical 3P 1 front connection 36

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	32.5 cm
Package 1 Length	55.5 cm
Package 1 Weight	1.833 kg

Unit Type of Package 2	S04
Number of Units in Package 2	7
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13.774 kg
Unit Type of Package 3	P12
Number of Units in Package 3	28
Package 3 Height	44 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	66 kg

Offer Sustainability

BVB	Accepted
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No