



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	FuPact: fixed ISFL160 - control: fuse carriers handle - vertical installation
Poles description	9 x 3P: mounting plate support: ISFL160 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Cubicle - width 650 mm depth 400 mm
Connection position	Rear connection
Number of vertical modules [50 mm]	11
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	550 mm
Width	500 mm
Net weight	1.18 kg
Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle FuPact ISFL160 fixed fuse carriers handle vertical 3P 9 rear connection on busbar 11

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	51 cm
Package 1 Length	56 cm
Package 1 Weight	1.186 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	16 cm
Package 2 Width	53.5 cm
Package 2 Length	82 cm
Package 2 Weight	8.139 kg

Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Height	47 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	207 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product