



## Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Plain
Installed device	TeSys: fixed D or K contactors <= 40 A - horizontal installation
Poles description	9 x 4P: modular rail support: D or K contactors <= 40 A horizontal installation

## Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Connection position	Direct connection
Number of vertical modules [50 mm]	3
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	150 mm
Width	500 mm
Net weight	0.68 kg
Quantity per set	Set of 1
Functional unit	600 mm PrismaSeT G floor-standing enclosure TeSys D or K contactors <= 40 A fixed horizontal 4P 9 direct 3 600 mm PrismaSeT G wall-mounted enclosure TeSys D or K contactors <= 40 A fixed horizontal 4P 9 direct 3 650 mm 400 mm PrismaSeT P cubicle TeSys D or K contactors <= 40 A fixed horizontal 4P 9 direct 3

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	16.4 cm
Package 1 Length	51.0 cm
Package 1 Weight	676.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	16.5 cm
Package 2 Width	17.5 cm
Package 2 Length	52.5 cm
Package 2 Weight	6.935 kg
Unit Type of Package 3	P12
Number of Units in Package 3	450
Package 3 Height	96.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	323.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product