



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct PrismaSeT PrismaSeT P cubicle
Type of front plate	Plain
Installed device	TeSys: fixed TeSys U - horizontal installation Altistart: ATS01N103/106FT Phaseo: LV/LV transformer
Poles description	4 x 3P: modular rail support: TeSys U horizontal installation

Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number of vertical modules [50 mm]	4
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	200 mm
Width	250 mm
Net weight	0.48 kg
Quantity per set	Set of 1
Functional unit	300 mm PrismaSeT G floor-standing duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm PrismaSeT G wall-mounted duct TeSys TeSys U fixed horizontal 3P 4 direct 4 300 mm PrismaSeT G floor-standing duct Altistart ATS01N103/106FT 19 4 300 mm PrismaSeT G wall-mounted duct Altistart ATS01N103/106FT 19 4 300 mm PrismaSeT G floor-standing duct Phaseo LV/LV transformer 4 300 mm PrismaSeT G wall-mounted duct Phaseo LV/LV transformer 4 400 mm 400 mm PrismaSeT P cubicle 4

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	21.000 cm
Package 1 Length	27.000 cm
Package 1 Weight	468.000 g
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	22.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	4.866 kg
Unit Type of Package 3	P12
Number of Units in Package 3	600
Package 3 Height	97.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	306.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations