

Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct PrismaSeT PrismaSeT P cubicle
Type of front plate	Plain
Installed device	TeSys: fixed TeSys U - horizontal installation
Poles description	4 x 3P: modular rail support: TeSys U horizontal installation

Complementary

Enclosure/cubicle description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number of vertical modules [50 mm]	5
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	250 mm
Width	250 mm
Net weight	0.58 kg
Quantity per set	Set of 1
Functional unit	300 mm PrismaSeT G floor-standing duct TeSys TeSys U fixed horizontal 3P 4 direct 5 300 mm PrismaSeT G wall-mounted duct TeSys TeSys U fixed horizontal 3P 4 direct 5 400 mm 400 mm PrismaSeT P cubicle 5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.6 cm
Package 1 Width	26.2 cm
Package 1 Length	26.2 cm
Package 1 Weight	584.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	16.5 cm
Package 2 Width	27.5 cm
Package 2 Length	28.0 cm
Package 2 Weight	6.008 kg
Unit Type of Package 3	P12

Number of Units in Package 3	240
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	155.0 kg

Offer Sustainability

BVB	Accepted
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No