



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Plain
Type of front plate	Plain

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Number of vertical modules [50 mm]	6
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	300 mm
Width	750 mm
Net weight	2.04 kg
Quantity per set	Set of 1
Functional unit	850 mm PrismaSeT G floor-standing enclosure

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	30 cm
Package 1 Length	75 cm
Package 1 Weight	2.093 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	7 cm
Package 2 Width	32 cm
Package 2 Length	79 cm
Package 2 Weight	8.804 kg
Unit Type of Package 3	P12

Number of Units in Package 3	20
Package 3 Height	27 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	55.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product