



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT P cubicle
Provided equipment	Door Handle Keylock (key 405) Hinge Other keylock and insert to be ordered separately
Enclosure mounting	Floor-standing
Type of door	Cut-out
IP degree of protection	IP30

## Complementary

Installation description	Cubicle - width 650 mm
Door opening side	Left
Number of locks	2
Door opening angle	120 °
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	2000 mm
Width	650 mm
Depth	35 mm
Net weight	17.36 kg
Surface finish	Textured Matt
Colour	White (RAL 9003)

## Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	70.0 cm
Package 1 Length	199.5 cm
Package 1 Weight	23.1 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	85.0 cm

Package 2 Width	120.0 cm
Package 2 Length	202.0 cm
Package 2 Weight	251.0 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations