



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Incoming connection block
Product name	PrismaSeT PrismaSeT G enclosure
Accessory / separate part category	Connection accessory
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA

Complementary

Location of connection	Bottom
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 850 mm Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Installed device	ComPact: fixed INS250 - control: direct front rotary handle horizontal installation ComPact: fixed INV250 - control: direct front rotary handle horizontal installation ComPact: fixed INV100 - control: direct front rotary handle horizontal installation ComPact: fixed NSX100...160 without earth leakage protection - control: toggle horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: toggle horizontal installation ComPact: fixed INV160 - control: direct front rotary handle horizontal installation ComPact: fixed INV200 - control: direct front rotary handle horizontal installation
[I _e] rated operational current	250 A
Net weight	1.48 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.500 cm
Package 1 Width	22.000 cm
Package 1 Length	23.500 cm
Package 1 Weight	1.409 kg
Unit Type of Package 2	P12
Number of Units in Package 2	90
Package 2 Height	83.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	138.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations