

Main

Range	Linergy
Range of product	Linergy
Product or component type	Auxiliary bus duct
Product name	Linergy TA
Range compatibility	PrismaSeT PrismaSeT P enclosure
IP degree of protection	IP20
Number of tap-off outlets	166 tap-off points with Faston connectors per linear meter
Provided equipment	1 lateral clamp 2 clamps 4 brass conductors with tap off point Insulating duct
Quantity per set	Set of 1

Complementary

Poles description	4P
Rated voltage	230 V
Installation direction	Vertical, operating position: lateral
Installation description	Cubicle duct - width 300 mm
[Ui] rated insulation voltage	660 V
[Ie] rated operational current	32 A
Length	1755 mm
Height	85 mm
Width	50 mm
Net weight	1.62 kg
Colour	Light grey (RAL 7035)

Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	9.0 cm
Package 1 Length	179.0 cm
Package 1 Weight	1.751 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Height	54.0 cm
Package 2 Width	180.0 cm
Package 2 Length	202.0 cm
Package 2 Weight	151.0 kg

Offer Sustainability

BVB	Accepted
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No