



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G duct
Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed device	Connection: earth bars Connection: terminal blocks
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Width	215 mm
Height	35 mm
Depth	82 mm
Net weight	0.46 kg
Quantity per set	2
Functional unit	300 mm PrismaSeT G floor-standing duct connection earth bars 300 mm PrismaSeT G wall-mounted duct connection earth bars 300 mm PrismaSeT G floor-standing duct connection terminal blocks 300 mm PrismaSeT G wall-mounted duct connection terminal blocks

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	10.5 cm
Package 1 Length	23.0 cm
Package 1 Weight	447.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	14
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.49 kg
Unit Type of Package 3	P12
Number of Units in Package 3	448
Package 3 Height	70.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	218.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product