



Main

| | |
|------------------------------------|--|
| Range | PrismaSeT |
| Range of product | PrismaSeT P PrismaSeT G |
| Product or component type | Rail |
| Accessory / separate part category | Installation accessory |
| Range compatibility | PrismaSeT PrismaSeT G PrismaSeT PrismaSeT P |
| Type of rail | Modular |
| Installed device | Acti 9: fixed modular device Multi9: fixed modular device ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle ComPact: fixed NSXm - control: toggle |
| Poles description | 1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA |

Complementary

| | |
|------------------------------------|---|
| Installation description | Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 850 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm |
| Number of vertical modules [50 mm] | 5 module(s): NG160 without earth leakage protection , direct in 650 mm Widecubicle 5 module(s): NG160 NA without earth leakage protection , direct in 650 mm Widecubicle 5 module(s): NG160 with earth leakage protection , direct in 650 mm Widecubicle 5 module(s): modular device in 600 mm Widefloor-standing enclosure 5 module(s): modular device in 600 mm Widewall-mounted enclosure 5 module(s): modular device in 850 mm Widefloor-standing enclosure 5 module(s): modular device in 650 mm Widecubicle 5 module(s): modular device in 555 mm WidePack enclosure |
| Provided equipment | 4 modular raisers |
| 9 mm pitches | 48 |
| Quantity per set | Set of 1 |
| Height | 35 mm |
| Width | 432 mm |
| Depth | 40 mm |
| Net weight | 0.14 kg |
| Colour | Natural |
| Material | Metal |

Environment

| | |
|------------------------|----------------------------|
| Standards | IEC 61439-2 IEC 61439-1 |
| Product certifications | ASTA |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.7 cm |
| Package 1 Width | 6.3 cm |
| Package 1 Length | 34.3 cm |
| Package 1 Weight | 160 g |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 15 |
| Package 2 Height | 15 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 2.78 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 120 |
| Package 3 Height | 28 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 33.5 kg |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |