



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Connection
Product name	PrismaSeT PrismaSeT P enclosure
Accessory / separate part category	Current distribution accessory
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA

Complementary

Cubicle-device connection	Linergy busbar
Poles description	4P
Installation description	Cubicle - width 650 mm
Cubicle depth	400 mm: front 400 + 400 mm: rear
Installed device	ComPact: fixed NS1600 - control: toggle vertical installation ComPact: fixed NS1600 - control: direct front rotary handle vertical installation ComPact: fixed NS1600 - control: motor mechanism vertical installation
[Ie] rated operational current	1600 A
Busbar cross section	80 x 10 mm
Height	150 mm
Width	550 mm
Depth	300 mm
Net weight	18.84 kg
Quantity per set	Set of 1
Functional unit	650 mm 800 mm PrismaSeT P cubicle ComPact NS1600 fixed toggle vertical 4P 1 rear connection on Canalis 16 650 mm 800 mm PrismaSeT P cubicle ComPact NS1600 fixed direct front rotary handle vertical 4P 1 rear connection on Canalis 16 650 mm 400 mm PrismaSeT P cubicle ComPact NS1600 fixed toggle vertical 4P 1 front connection on adaptor 14 650 mm 400 mm PrismaSeT P cubicle ComPact NS1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 650 mm 800 mm PrismaSeT P cubicle ComPact NS1600 fixed motor mechanism vertical 4P 1 rear connection on Canalis 16 650 mm 400 mm PrismaSeT P cubicle ComPact NS1600 fixed motor mechanism vertical 4P 1 front connection on adaptor 14

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	12.0 cm
Package 1 Length	54.0 cm
Package 1 Weight	18.33 kg
Unit Type of Package 2	P12
Number of Units in Package 2	12

Package 2 Height	27.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	240.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations