



Main

Range	Linergy
Range of product	Linergy
Product or component type	Busbar
Product name	Linergy BS
Range compatibility	PrismaSeT PrismaSeT P enclosure
Busbar description	Flat bar
Quantity per set	Set of 1

Complementary

Installation direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ie] rated operational current	1000 A at 35 °C
[Icw] rated short-time withstand current	25 KA (1 s) for 2 supports 50 kA (1 s) for 3 supports
Permissible current	1000 A at 35 °C: ≤ IP31 900 A at 35 °C: > IP31
Busbar cross section	80 x 5 mm
Length	2000 mm
Width	80 mm
Depth	5 mm
Net weight	7.9 kg
Colour	Natural
Type of busbar connection	Without hole

Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	14.5 cm
Package 1 Length	212.0 cm
Package 1 Weight	7.751 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	80
Package 2 Height	35.0 cm
Package 2 Width	120.0 cm

Package 2 Length	202.0 cm
Package 2 Weight	645.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins