

Main

Range	Linergy
Range of product	Linergy
Product or component type	Connection
Product name	Linergy LGYE
Product name	PrismaSeT PrismaSeT P enclosure Linergy Linergy LGYE busbar
Provided equipment	Fixing frame Fixing elements
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA




Complementary

Cubicle-device connection	Linergy busbar
Installed device	Connection: busbar vertical shifted installation
[Ie] rated operational current	1600 A
Height	140 mm
Width	80 mm
Depth	4 mm
Net weight	0.8 kg
Quantity per set	Set of 1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.000 cm
Package 1 Length	16.000 cm
Package 1 Weight	759.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.888 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
BVB	 Accepted
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	39