



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Insulated flexible bar
Product name	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P enclosure PrismaSeT Prisma iPM L enclosure PrismaSeT Prisma iPM M enclosure
Accessory / separate part category	Current distribution accessory
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA

Complementary

Installation description	Cubicle Floor-standing enclosure Wall-mounted enclosure
Installed device	ComPact: NSX100 + INS100 ComPact: INS100...160 ComPact: INV100 ComPact: INV160 EasyPact: CVS100...160
[Ie] rated operational current	200 A
Busbar cross section	20 x 2 mm
Length	1800 mm
Net weight	1.38 kg
Quantity per set	Set of 1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.700 cm
Package 1 Width	12.000 cm
Package 1 Length	193.500 cm
Package 1 Weight	1.230 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	130
Package 2 Height	31.000 cm
Package 2 Width	120.000 cm
Package 2 Length	200.000 cm
Package 2 Weight	189.250 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations