



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT G enclosure
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert to be ordered separately 2 hinge
Type of door	Transparent
IP degree of protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

Complementary

Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door opening side	Reversible
Number of locks	1
Door opening angle	130 °
Number of vertical modules [50 mm]	9
Enclosure material	Handle: polyamide Glass Cover frame: treated sheet steel
Quantity per set	Set of 1
Height	480 mm
Width	600 mm
Depth	36 mm
Net weight	3.68 kg
Material	Glass
Surface finish	Textured Matt
Colour	White (RAL 9003)

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	54.000 cm
Package 1 Length	64.500 cm
Package 1 Weight	4.508 kg

Unit Type of Package 2	P12
Number of Units in Package 2	20
Package 2 Height	90.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	101.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations