



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT G enclosure
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert to be ordered separately 3 hinge
Type of door	Plain
IP degree of protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

## Complementary

Installation description	Floor-standing enclosure - width 850 mm
Door opening side	Reversible
Number of locks	3
Door opening angle	130 °
Number of vertical modules [50 mm]	30
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	1530 mm
Width	850 mm
Depth	40 mm
Net weight	15 kg
Surface finish	Matt Textured
Colour	White (RAL 9003)

## Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	89.000 cm
Package 1 Length	160.000 cm
Package 1 Weight	18.319 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	85.000 cm

Package 2 Width	120.000 cm
Package 2 Length	202.000 cm
Package 2 Weight	211.200 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes