

## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Rear panel
Device application	Low voltage electrical distribution
Enclosure type	Functional enclosure delivered in kit form
Additional information	Can be combined side by side and one on top of another
Type of front plate	Without
Number of vertical modules [50 mm]	27
Number of 18 mm modules per row	24

## Complementary

[Ui] rated insulation voltage	1000 V on main rear busbars conforming to IEC 61439-2
Network frequency	50/60 Hz
[In] rated current	630 A at 40 °C conforming to IEC 61439-2
[Icw] rated short-time withstand current	25 kA 1 s conforming to IEC 61439-2
[Ipk] rated peak withstand current	53 kA conforming to IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	1450 mm
Depth	260 mm
Net weight	12.52 kg
Quantity per set	Set of 1

## Environment

IP degree of protection	IP55 with door
IK degree of protection	IK10 with door conforming to EN/IEC 62262
Mechanical robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	49.0 cm
Package 1 Length	142.0 cm
Package 1 Weight	12.423 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	38.0 cm
Package 2 Width	120.0 cm
Package 2 Length	202.0 cm
Package 2 Weight	100.0 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
BVB	<a href="#">Accepted</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Take-back	No