



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT G enclosure
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert to be ordered separately 2 hinge
Type of door	Plain
IP degree of protection	IP55

Complementary

Installation description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door opening side	Reversible
Number of locks	3
Door opening angle	180 °
Number of vertical modules [50 mm]	7
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	450 mm
Width	600 mm
Depth	26 mm
Net weight	8.18 kg
Surface finish	Textured Matt
Colour	White (RAL 9003)

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	44.0 cm
Package 1 Length	60.0 cm
Package 1 Weight	7.937 kg
Unit Type of Package 2	P12
Number of Units in Package 2	16
Package 2 Height	75.0 cm
Package 2 Width	80.0 cm

Package 2 Length	120.0 cm
Package 2 Weight	139.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations