



### Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Rear panel Door
Device application	Low voltage electrical distribution
Enclosure type	Functional enclosure delivered in kit form
Provided equipment	1 x door for enclosure
Additional information	Can be combined side by side and one on top of another
Type of front plate	Without
Number of vertical modules [50 mm]	15
Number of 18 mm modules per row	10

### Complementary

[Ui] rated insulation voltage	1000 V
[In] rated current	630 A at 40 °C conforming to IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Smooth Matt
Colour	White (RAL 9001)
Width	300 mm
Height	850 mm
Depth	260 mm
Net weight	15.04 kg
Quantity per set	Set of 1

### Environment

IP degree of protection	IP55 with door
IK degree of protection	IK10 with door conforming to EN/IEC 62262
Mechanical robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	33.5 cm
Package 1 Length	84 cm
Package 1 Weight	14.751 kg
Unit Type of Package 2	P12
Number of Units in Package 2	4
Package 2 Height	35 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	71 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations