



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Door Rear panel
Device application	Low voltage electrical distribution
Enclosure type	Functional enclosure delivered in kit form
Provided equipment	1 x door for enclosure
Additional information	Can be combined side by side and one on top of another
Type of front plate	Without
Number of vertical modules [50 mm]	23
Number of 18 mm modules per row	10

Complementary

[Ui] rated insulation voltage	1000 V
[In] rated current	630 A at 40 °C conforming to IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Smooth
Colour	White (RAL 9001)
Width	300 mm
Height	1250 mm
Depth	260 mm
Net weight	21.44 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP55 with door
IK degree of protection	IK10 with door conforming to EN/IEC 62262
Mechanical robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.500 cm
Package 1 Width	37.000 cm
Package 1 Length	124.000 cm
Package 1 Weight	21.500 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	14
Package 2 Height	69.000 cm
Package 2 Width	120.000 cm
Package 2 Length	200.000 cm
Package 2 Weight	322.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations