



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Side panel
Range compatibility	PrismaSeT PrismaSeT G enclosure
Device application	Low voltage electrical distribution
Enclosure type	Metal enclosure
Installation description	Wall-mounted enclosure - width 600 mm
Kit composition	2 side panel
Number of vertical modules [50 mm]	23
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure
Product certifications	ASTA

## Complementary

Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Special colour options	Yes
Width	250 mm
Height	1250 mm
Net weight	7.9 kg
Quantity per set	Set of 1

## Environment

IP degree of protection	IP55 for enclosure
IK degree of protection	IK10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	23.0 cm
Package 1 Length	124.0 cm
Package 1 Weight	8.33 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	21.0 cm
Package 2 Width	120.0 cm
Package 2 Length	202.0 cm
Package 2 Weight	76.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product