



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Partial door
Range compatibility	PrismaSeT PrismaSeT G enclosure
Provided equipment	Door 2 hinge 8 mm male triangle insert Insulating plain mounting plate
Type of door	Cut-out
IP degree of protection	IP55

Complementary

Installation description	Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 600 mm
Number of locks	3
Door opening angle	180 °
Number of vertical modules [50 mm]	4
Additional information	Dimensions of the two holes are 200 x 112 mm
Quantity per set	Set of 1
Height	200 mm
Width	600 mm
Depth	26 mm
Net weight	5.18 kg
Surface finish	Textured Matt
Colour	White (RAL 9003)

Environment

IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	24.5 cm
Package 1 Length	59.5 cm
Package 1 Weight	5.18 kg
Unit Type of Package 2	P12
Number of Units in Package 2	6
Package 2 Height	28.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	43.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations