



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Roof
Range compatibility	PrismaSeT PrismaSeT P enclosure
Device application	Low voltage electrical distribution
Enclosure type	Metal enclosure
Installation description	Cubicle duct - width 300 mm, depth 400 mm
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure
Product certifications	ASTA

Complementary

Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured Matt
Colour	White (RAL 9003)
Special colour options	Yes
Width	300 mm
Depth	400 mm
Net weight	1.36 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP30 for enclosure
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	40.500 cm
Package 1 Length	40.500 cm
Package 1 Weight	1.474 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	30
Package 2 Height	35.000 cm
Package 2 Width	81.500 cm
Package 2 Length	124.000 cm
Package 2 Weight	56.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations