



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT P cubicle duct
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert to be ordered separately 2 hinge
Enclosure mounting	Floor-standing
Type of door	Plain
IP degree of protection	IP30

Complementary

Installation description	Cubicle duct - width 400 mm
Door opening side	Reversible
Number of locks	2
Door opening angle	120 °
Number of vertical modules [50 mm]	36
Enclosure material	Treated sheet steel
Quantity per set	Set of 1
Height	1925 mm
Width	400 mm
Depth	30 mm
Net weight	12.44 kg
Surface finish	Matt Textured
Colour	White (RAL 9003)

Environment

IK degree of protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	46.5 cm
Package 1 Length	198.5 cm
Package 1 Weight	13.65 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	20
Package 2 Height	85.0 cm
Package 2 Width	120.0 cm

Package 2 Length	202.0 cm
Package 2 Weight	293.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations