

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Door
Range compatibility	PrismaSeT PrismaSeT P cubicle
Provided equipment	Door Handle Keylock (key 405) Other keylock and insert to be ordered separately 4 hinge Polyurethane joint
Enclosure mounting	Floor-standing
Type of door	Transparent
IP degree of protection	IP55

Complementary

Installation description	Cubicle - width 650 mm
Door opening side	Reversible
Number of locks	3
Door opening angle	120 °
Number of vertical modules [50 mm]	36
Enclosure material	Glass Treated sheet steel
Quantity per set	Set of 1
Height	1925 mm
Width	650 mm
Net weight	24.76 kg
Surface finish	Matt Textured
Colour	White (RAL 9003)

Environment






IK degree of protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	69.500 cm
Package 1 Length	198.500 cm
Package 1 Weight	26.052 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	84.000 cm
Package 2 Width	120.000 cm

Package 2 Length	202.000 cm
Package 2 Weight	281.000 kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	53da272d-b040-4851-8009-84e538bee882
BVB	 Accepted
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No