



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P duct
Type of front plate	Plain

Complementary

Enclosure/cubicle description	Cubicle - width 300 mm
Number of vertical modules [50 mm]	1
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Painted steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	Green (RAL 6029)
Height	50 mm
Width	300 mm
Net weight	0.18 kg
Quantity per set	Set of 1
Functional unit	300 mm PrismaSeT P cubicle

Environment

IP degree of protection	IP31 IP41 IP55
-------------------------	----------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	4.7 cm
Package 1 Length	31.5 cm
Package 1 Weight	614.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.65 kg

Unit Type of Package 3	P12
Number of Units in Package 3	192
Package 3 Height	44.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	134.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations