



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Roof
Range compatibility	PrismaSeT PrismaSeT P enclosure
Device application	Low voltage electrical distribution
Enclosure type	Metal enclosure
Installation description	Cubicle - width 400 mm, depth 600 mm
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure
Product certifications	ASTA

## Complementary

Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Special colour options	Yes
Width	400 mm
Depth	600 mm
Net weight	2.72 kg
Quantity per set	Set of 1

## Environment

IP degree of protection	IP55 for enclosure
IK degree of protection	IK10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	42.0 cm
Package 1 Length	62.5 cm
Package 1 Weight	2.757 kg
Unit Type of Package 2	P12
Number of Units in Package 2	36
Package 2 Height	87.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	111.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations