



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Ventilated roof
Range compatibility	PrismaSeT PrismaSeT P enclosure
Device application	Low voltage electrical distribution
Enclosure type	Metal enclosure
Installation description	Cubicle - width 650 mm, depth 600 mm
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure
Product certifications	ASTA

Complementary

Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Special colour options	Yes
Width	650 mm
Depth	600 mm
Net weight	5.24 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP30 for enclosure
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	61.000 cm
Package 1 Length	81.000 cm
Package 1 Weight	3.806 kg
Unit Type of Package 2	P12
Number of Units in Package 2	15
Package 2 Height	47.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	70.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes