



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Plinth raiser
Range compatibility	PrismaSeT PrismaSeT G enclosure
Product compatibility	IP31 enclosure IP41 enclosure

Complementary

Installation description	Floor-standing enclosure - width 600 mm Extension enclosure - width 600 mm
Quantity per set	Set of 1
Height	100 mm
Width	600 mm
Depth	260 mm
Net weight	2.02 kg
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	10.800 cm
Package 1 Length	61.000 cm
Package 1 Weight	2.372 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	32.000 cm
Package 2 Width	59.000 cm
Package 2 Length	79.500 cm
Package 2 Weight	25.675 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	144.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	218.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product