



### Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Canopy
Accessory / separate part category	Enclosure accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
IP degree of protection	IP31

### Complementary

Installation description	Floor-standing enclosure + duct - width 600 + 300 mm Wall-mounted enclosure + duct - width 600 + 300 mm
Quantity per set	Set of 1
Height	45 mm
Width	900 mm
Depth	280 mm
Net weight	3.84 kg
Surface finish	Matt Textured
Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	29.0 cm
Package 1 Length	92.0 cm
Package 1 Weight	3.676 kg
Unit Type of Package 2	P12
Number of Units in Package 2	21
Package 2 Height	88.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	89.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product