



## Main

|                                    |                            |
|------------------------------------|----------------------------|
| Range of product                   | PrismaSeT G                |
| Range                              | PrismaSeT                  |
| Range compatibility                | PrismaSeT PrismaSeT G door |
| IP degree of protection            | IP43                       |
| Product or component type          | Gasket                     |
| Accessory / separate part category | Sealing accessory          |
| Provided equipment                 | 1 self-adhesive gasket     |

## Complementary

|                                    |  |
|------------------------------------|--|
| Enclosure/cubicle description      | Wall-mounted enclosure - width 300 mm<br>Wall-mounted duct - width 300 mm<br>Wall-mounted enclosure - width 600 mm<br>Wall-mounted enclosure - width 850 mm<br>Floor-standing enclosure - width 300 mm<br>Floor-standing duct - width 300 mm<br>Floor-standing enclosure - width 600 mm<br>Floor-standing enclosure - width 850 mm |
| Number of vertical modules [50 mm] | 6<br>9<br>12<br>15<br>18.0<br>21<br>24<br>27<br>30<br>33   |
| Quantity per set                   | Set of 1   |
| Length                             | 5300 mm  |
| Net weight                         | 0.06 kg  |
| Colour                             | Black (RAL 7016)   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1.4 cm    |
| Package 1 Width              | 15.5 cm   |
| Package 1 Length             | 17.0 cm   |
| Package 1 Weight             | 123.0 g   |
| Unit Type of Package 2       | S04       |
| Number of Units in Package 2 | 100       |
| Package 2 Height             | 30.0 cm   |
| Package 2 Width              | 40.0 cm   |
| Package 2 Length             | 60.0 cm   |
| Package 2 Weight             | 12.718 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | No need of specific recycling operations   |
| PVC free                   | Yes  |