

Product data sheet

Characteristics

LVS08872

Gland plate, PrismaSeT G, membrane type, 29 entries with dia 5 to 26mm, Insulated, IP55, white, RAL 9003



Main

| | |
|------------------------------------|--|
| Range of product | PrismaSeT G |
| Range | PrismaSeT |
| Range compatibility | PrismaSeT PrismaSeT G gland plate |
| Product or component type | Gland plate |
| Accessory / separate part category | Enclosure accessory |
| Product compatibility | IP43 enclosure IP31 enclosure IP55 enclosure IP30 enclosure |

Complementary

| | |
|-------------------------------|--|
| Enclosure/cubicle description | Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 600 mm Wall-mounted duct - width 300 mm Floor-standing duct - width 300 mm |
| Type of gland plate | Membrane |
| Material | Insulated material |
| Cable entry number | 4 diameter: 5...7 mm 12 diameter: 10...14 mm 4 diameter: 14...20 mm 1 diameter: 20...26 mm 4 diameter: 8...14 mm 4 diameter: 7...14 mm |
| Quantity per set | Set of 1 |
| Depth | 180 mm |
| Net weight | 0.28 kg |
| Colour | White (RAL 9003) |

Environment

| | |
|-------------------------|------|
| IP degree of protection | IP55 |
|-------------------------|------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 8.4 cm |
| Package 1 Length | 21.7 cm |
| Package 1 Weight | 278.0 g |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 5.802 kg |
| Unit Type of Package 3 | P12 |

| | |
|------------------------------|----------|
| Number of Units in Package 3 | 240 |
| Package 3 Height | 44.0 cm |
| Package 3 Width | 80.0 cm |
| Package 3 Length | 120.0 cm |
| Package 3 Weight | 81.5 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| PVC free | Yes |