



## Main

Range of product	PrismaSeT G
Range	PrismaSeT
Range compatibility	PrismaSeT PrismaSeT G enclosure
Product or component type	Gland plate
Accessory / separate part category	Enclosure accessory
Product compatibility	IP31 enclosure IP30 enclosure IP43 enclosure
Provided equipment	1 gland plate

## Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm
Type of gland plate	Plain
Mounting location	Plinth
Material	Metal
Quantity per set	Set of 1
Width	600 mm
Depth	180 mm
Net weight	0.84 kg
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

## Environment

IP degree of protection	IP20
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	15.9 cm
Package 1 Length	56.4 cm
Package 1 Weight	811.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	14
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	11.912 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product