



## Main

Range of product	PrismaSeT G
Range	PrismaSeT
Range compatibility	PrismaSeT PrismaSeT G enclosure
Product or component type	Gland plate
Accessory / separate part category	Enclosure accessory
Product compatibility	IP31 enclosure IP30 enclosure IP43 enclosure
Provided equipment	1 gland plate

## Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm
Type of gland plate	Plain
Mounting location	Plinth
Material	Metal
Quantity per set	Set of 1
Width	827 mm
Depth	160 mm
Net weight	1.22 kg
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

## Environment

IP degree of protection	IP20
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	16 cm
Package 1 Length	81.5 cm
Package 1 Weight	1.159 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	16 cm
Package 2 Width	51.5 cm
Package 2 Length	81 cm
Package 2 Weight	6.9 kg
Unit Type of Package 3	P12
Number of Units in Package 3	30
Package 3 Height	67 cm

Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	64 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product